

46142070 Cut Sheet



WERMA EvoSIGNAL Midi TwinFLASH series LED audible-visual signal beacon, 110 dB at 1m, (10) selectable tone(s), double flash or EVS (Enhanced Visibility System) flashing (random flashing), clear/white, 85mm, 12/24 VAC/VDC, IP66. Requires mounting adapter.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/46142070>

Technical Specifications

Brand	WERMA
Item	Audible-visual signal beacon
Series	EvoSIGNAL Midi TwinFLASH
Bulb Type	LED
Operator Size	85mm
Operator Color	Clear
Light Color(s)	Clear/white
Light Function	Double flash (ON 30ms, Off 160ms, ON 30ms, Off 740ms, 1 Hz flash frequency) or EVS (Enhanced Visibility System) flashing (random flashing)
Housing Material	Polycarbonate

Material	ABS/polycarbonate
Loudness Decibel	110 dB at 1m
Tone Frequency	3.3 kHz
Tone Type	(10) selectable
Touch to Acknowledge	No
Number of Alarms	10
Voltage Rating	12/24 VAC/VDC
Mounting	Modular
IP Rating	IP66
Requires	Mounting adapter

Agency Approvals

UL Listed File #	E164155
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/46142070.pdf>
See store item page for other formats.