

4825U200 Cut Sheet



Socomec DIRIS A20 power meter, current and voltage input, 3-line backlit LCD, optional plug-in modules for output, 110-240 VAC/120-250 VDC operating voltage.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/4825U200>

Technical Specifications

Brand	Socomec
Item	Power meter
Series	DIRIS A20
Display Type	3-line backlit LCD
Input Current Signal Range	0-5A
Input Voltage Signal Range	50-500 VAC (L-L), 28-289 VAC (L-N)
Operating Voltage	110-240 VAC/120-250 VDC
Accuracy	0.5% active power
System Configuration	1-phase, 2-phase, 3-phase 3-wire, 3-phase 4-wire
Mounting	Panel
Mounting Hole Size	92mm x 92mm
Additional Information	An integrated test function can be utilized to detect incorrect wiring, accepts up to 2 output or communication plugin modules

Agency Approvals

UL Listed File #	E257746
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/4825U200.pdf>
See store item page for other formats.