

4UHD9015718FTC Cut Sheet



Hammond disconnect enclosure, NEMA 12, right flange, 90 x 157 x 18in (HxWxD), freestanding, carbon steel, ANSI 61 gray, powder coat finish, 4-door, 3-point padlocking handle.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/4UHD9015718FTC>

Technical Specifications

Brand	Hammond
Item	Disconnect enclosure
Slope Top	No
NEMA Rating	12
IP Rating	IP54
Disconnect Mounting	Right flange
Nominal Enclosure Dimensions	90 x 157 x 18in (HxWxD)
Enclosure Height	90.13in
Enclosure Width	156.50in
Enclosure Depth	19.35in
Mounting	Freestanding
Dual Access	No
Knockouts	No

Material	Carbon steel
Color	ANSI 61 gray
Finish	Powder coat
Cover Type	4-door
Hinge Type	Lift-off hinges
Number of Hinges Per Door	3
Latch Type	3-point padlocking handle
Padlockable	Yes
Subpanel	(2) subpanels included
Additional Information	Purchase operating mechanism, disconnect switch or circuit breaker, and operating handle from disconnect supplier

Agency Approvals

UL Listed File #	E65324
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	LR21001
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document