

# 4UHD9015718N4SS Cut Sheet



Hammond disconnect enclosure, NEMA 3R/4/4X/12/13, right flange, 90 x 157 x 18in (HxWxD), freestanding, 304 stainless steel, #4 brush finish, 4-door, 3-point padlocking handle.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/4UHD9015718N4SS>

## Technical Specifications

<b>Brand</b>	Hammond
<b>Item</b>	Disconnect enclosure
<b>Slope Top</b>	No
<b>Vented</b>	No
<b>NEMA Rating</b>	3R/4/4X/12/13
<b>IP Rating</b>	IP66
<b>Disconnect Mounting</b>	Right flange
<b>Nominal Enclosure Dimensions</b>	90 x 157 x 18in (HxWxD)
<b>Enclosure Height</b>	90.13in
<b>Enclosure Width</b>	156.50in
<b>Enclosure Depth</b>	19.35in

<b>Mounting</b>	Freestanding
<b>Integral Mounting Feet</b>	No
<b>Material</b>	304 stainless steel
<b>Finish</b>	#4 brush
<b>Cover Type</b>	4-door
<b>Hinge Type</b>	Lift-off hinges
<b>Number of Hinges Per Door</b>	3
<b>Latch Type</b>	3-point padlocking handle
<b>Padlockable</b>	Yes
<b>Keylocking</b>	No
<b>Subpanel</b>	(2) subpanels included

## Agency Approvals

<b>UL Listed File #</b>	E65324
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	LR21001
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/4UHD9015718N4SS.pdf>  
See store item page for other formats.