

500KC112B Cut Sheet



Minerallac screw-on beam clamp conduit hanger assembly, spring clip, back mount, 100 lbs. Package of 100. For use with flanges up to 1/2in and 1-1/2in conduit.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/500KC112B>

Technical Specifications

Brand	Minerallac	Load Rating	100 lbs
Item	Conduit hanger assembly	Outside Diameter	1.73in-1.91in
Mount Type	Screw-on beam clamp	Rigid Metallic Conduit (RMC) Trade Size	1-1/2in
Hanger Type	Spring clip	Electrical Metallic Tubing (EMT) Trade Size	1-1/2in
Mount Side	Back	Intermediate Metallic Conduit (IMC) Trade Size	1-1/2in
Material	Spring steel	Quantity per Pack	100
Finish	Zinc phosphate plated	For Use With	Flanges up to 1/2in and 1-1/2in conduit
Mounting Holes	1/4-20 UNC bottom and 3/8in pass through bottom		
Maximum Flange Thickness	1/2in		
Set Screw Size	1/4in-20 UNC		

Agency Approvals

CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document