

# 500KC1234 Cut Sheet



Minerallac screw-on beam clamp conduit hanger assembly, spring clip, bottom mount, 100 lbs. Package of 100. For use with flanges up to 1/2in and 1/2 or 3/4in conduit.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/500KC1234>

## Technical Specifications

Brand	Minerallac
Item	Conduit hanger assembly
Mount Type	Screw-on beam clamp
Hanger Type	Spring clip
Mount Side	Bottom
Material	Spring steel
Finish	Zinc phosphate plated
Mounting Holes	1/4-20 UNC back and #10-24 UNC back
Maximum Flange Thickness	1/2in
Set Screw Size	1/4in-20 UNC
Load Rating	100 lbs
Outside Diameter	0.70in-1.05in

Tubing Size	3/4in, 13/16in, 7/8in, 15/16in and 1in
Rigid Metallic Conduit (RMC) Trade Size	1/2in and 3/4in
Electrical Metallic Tubing (EMT) Trade Size	1/2in and 3/4in
Intermediate Metallic Conduit (IMC) Trade Size	1/2in and 3/4in
Reduced Wall Flexible Metal Conduit Trade Size	3/8in and 1/2in
Liquid-tight Flexible Metal Conduit (LFMC) Trade Size	1/2in and 3/4in
Quantity per Pack	100
For Use With	Flanges up to 1/2in and 1/2 or 3/4in conduit

## Agency Approvals

CE	None
CSA File #	None
RoHS Status	No
EU REACH	<a href="#">View EU REACH document</a>