

500 Cut Sheet



Minerallac screw-on beam clamp, 100 lbs. Package of 100. For use with flanges up to 1/2in and up to 3/8 threaded rod with nut (nut not included).

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/500>

Technical Specifications

Brand	Minerallac
Item	Clamp
Clamp Type	Beam
Attachment Type	Screw-on
Mounting Holes	1/4in pass through bottom, 3/8in pass through bottom, 1/4-20 UNC bottom, 1/4-20 UNC back and #10-24 UNC back
Load Rating	100 lbs
Material	Spring steel
Finish	Zinc phosphate plated
Maximum Flange Thickness	1/2in
Set Screw Size	1/4in-20 UNC
Quantity per Pack	100
For Use With	Flanges up to 1/2in and up to 3/8 threaded rod with nut (nut not included)

Agency Approvals

CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document