

5204008U Cut Sheet



Metal Work BIT air combination unit, filter-regulator-lubricator, 1/4in female NPT inlet(s), 1/4in female NPT outlet(s), 0–120 psig range, clear technopolymer bowl, manual/semi-automatic drain.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/5204008U>

Technical Specifications

Brand	Metal Work
Item	Combination unit
Working Fluid	Pneumatic
Series	BIT
Configuration	Filter-regulator-lubricator
Inlet Port	1/4in female NPT
Outlet Port	1/4in female NPT
Pressure Range	0–120 psig

Bowl Material	Clear technopolymer
Drain Type	Manual/semi-automatic
Clog Indicator	No
Manual Shutoff Valve	No
Padlockable	No
Soft Start Valve	No
Pressure Switch	No
Includes	Replaceable 20 micron filter element

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/5204008U.pdf>
See store item page for other formats.