

5205005U Cut Sheet



Metal Work BIT air filter-regulator, 1/4in female NPT inlet(s), 1/4in female NPT outlet(s), 0–60 psig range, manual/semi-automatic drain, clear technopolymer bowl. For use with Metal Work BIT series air prep components.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/5205005U>

Technical Specifications

Brand	Metal Work
Item	Filter-regulator
Working Fluid	Pneumatic
Series	BIT
Inlet Port	1/4in female NPT
Outlet Port	1/4in female NPT
Drain Port	G1/8 female BSPP

Pressure Range	0–60 psig
Drain Type	Manual/semi-automatic
Bowl Material	Clear technopolymer
Bowl Guard	No
Sight Gauge	No
For Use With	Metal Work BIT series air prep components
Includes	Replaceable 20 micron filter element

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/5205005U.pdf>
See store item page for other formats.