

5205011U Cut Sheet



Metal Work BIT air filter-regulator, 1/4in female NPT inlet(s), 1/4in female NPT outlet(s), 0–180 psig range, manual/semi-automatic drain, clear technopolymer bowl. For use with Metal Work BIT series air prep components.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/5205011U>

Technical Specifications

| | |
|----------------------|------------------|
| Brand | Metal Work |
| Item | Filter-regulator |
| Working Fluid | Pneumatic |
| Series | BIT |
| Inlet Port | 1/4in female NPT |
| Outlet Port | 1/4in female NPT |
| Drain Port | G1/8 female BSPP |

| | |
|-----------------------|---|
| Pressure Range | 0–180 psig |
| Drain Type | Manual/semi-automatic |
| Bowl Material | Clear technopolymer |
| Bowl Guard | No |
| Sight Gauge | No |
| For Use With | Metal Work BIT series air prep components |
| Includes | Replaceable 20 micron filter element |

Agency Approvals

| | |
|-----------------------------|---|
| UL Listed File # | None |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | None |
| CSA File # | None |
| RoHS Status | Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below) |
| EU REACH | View EU REACH document |
| Other | RoHS Statement |

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/5205011U.pdf>
See store item page for other formats.