

52350 Cut Sheet



Murrelektronik multi-mode relay timer, 0.1 to 300 seconds selectable timing range, 24 VDC operating voltage, 6A contact rating, (1) SPST timed relay output(s), 35mm DIN rail mount, screw terminal(s).

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/52350>

Technical Specifications

Brand	Murrelektronik
Item	Relay timer
Timer Type	Multi-mode
Timing Range	0.1 to 300 seconds selectable
Operating Voltage	24 VDC
Timer Output Type(s)	(1) SPST timed relay
Timer Function(s)	<ul style="list-style-type: none">• on-delay• off-delay• single-shot• sym. blinking pause starting• sym. blinking modulation
Contact Rating	6A
Mounting	35mm DIN rail
Connector Type	Screw terminal(s)

Agency Approvals

UL Listed File #	None
UL Recognized File #	E140415
UL Hazardous File #	None
CE	View CE declarations
CSA File #	1252427
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document