

52519 Cut Sheet



Murrelektronik optocoupler relay, 35mm DIN rail mount, finger-safe, 10-53 VDC input voltage, SPST, (1) N.O. MOSFET, 6A contact rating, 5-48 VDC load voltage, screw terminal(s), LED indicator(s).

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/52519>

Technical Specifications

Brand	Murrelektronik
Item	Relay
Relay Type	Optocoupler
Mounting	35mm DIN rail
Relay Housing Type	Finger-safe
Input Voltage	10-53 VDC
Relay Configuration	SPST
Output Type	(1) N.O. MOSFET
Load Voltage	5-48 VDC
Contact Rating	6A
Connector Type	Screw terminal(s)
Indicator	LED

Agency Approvals

UL Listed File #	None
UL Recognized File #	E140415
UL Hazardous File #	None
CE	View CE declarations
CSA File #	1252427
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/52519.pdf>
See store item page for other formats.