

5361 Cut Sheet



Bryant industrial heavy duty single straight blade receptacle, 20A, 125 VAC, 1-phase, 2-pole, 3-wire, NEMA 5-20, nylon housing, brown.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/5361>

Technical Specifications

| | |
|------------------------|-----------------------|
| Brand | Bryant |
| Item | Receptacle |
| Application | Industrial heavy duty |
| Receptacle Type | Single |
| Blade Type | Straight |
| With Cap | No |
| Self-grounding | Yes |
| Amperage Rating | 20A |
| Voltage Rating | 125 VAC |

| | |
|-------------------------|-----------------------------|
| Number of Phases | 1 |
| Number of Poles | 2 |
| Number of Wires | 3 |
| Wire Size | 14-10 AWG solid or stranded |
| Copper Wire Only | Yes |
| Configuration | NEMA 5-20 |
| Housing Material | Nylon |
| Color | Brown |

Agency Approvals

| | |
|-----------------------------|--|
| UL Listed File # | E2258 |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | View CE declarations |
| CSA File # | 016215 |
| RoHS Status | Yes (See CE Doc) |
| EU REACH | View EU REACH document |

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/5361.pdf>
See store item page for other formats.