

54741 Cut Sheet

Viking hand tap, M3 X 0.50 UNC, high-speed steel (HSS), bright finish.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/54741>

Technical Specifications

Brand	Viking
Item	Hand tap
Thread	M3 X 0.50 UNC
Number of Flutes	3
Flute Style	Straight flute
Tap Limit	D3

Overall Length	2.0in (51mm)
Tap Drill Size	2.5mm
Material	High-speed steel (HSS)
Finish	Bright
For Use On	Stainless steel, iron and steel
Application	Thread making

Agency Approvals

UL Listed File #	N/A
UL Recognized File #	N/A
UL Hazardous File #	N/A
CE	None
CSA File #	N/A
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement