

# 54761 Cut Sheet

Viking hand tap, M4 X 0.70 UNC, high-speed steel (HSS), bright finish.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/54761>

## Technical Specifications

Brand	Viking	Overall Length	2.0in (51mm)
Item	Hand tap	Tap Drill Size	3.3mm
Thread	M4 X 0.70 UNC	Material	High-speed steel (HSS)
Number of Flutes	4	Finish	Bright
Flute Style	Straight flute	For Use On	Stainless steel, iron and steel
Tap Limit	D4	Application	Thread making

## Agency Approvals

UL Listed File #	N/A
UL Recognized File #	N/A
UL Hazardous File #	N/A
CE	None
CSA File #	N/A
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	<a href="#">View EU REACH document</a>
Other	<a href="#">RoHS Statement</a>