

54931 Cut Sheet



Viking hand tap, M20 X 2.50 UNC, high-speed steel (HSS), bright finish.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/54931>

Technical Specifications

Brand	Viking	Overall Length	4.5in (114mm)
Item	Hand tap	Tap Drill Size	17.5mm
Thread	M20 X 2.50 UNC	Material	High-speed steel (HSS)
Number of Flutes	4	Finish	Bright
Flute Style	Straight flute	For Use On	Stainless steel, iron and steel
Tap Limit	D7	Application	Thread making

Agency Approvals

UL Listed File #	N/A
UL Recognized File #	N/A
UL Hazardous File #	N/A
CE	None
CSA File #	N/A
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement