

# 55081902 Cut Sheet



Southwire Gaflex flexible metallic conduit, reduced wall steel, 3/4in trade size, UL-1 Listed, 100ft/30.4m coil length.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/55081902>

---

## Technical Specifications

|                             |  |
|-----------------------------|--|
| <b>Brand</b>                | Southwire  |
| <b>Series</b>               | Gaflex   |
| <b>Item</b>                 | Conduit  |
| <b>Conduit Type</b>         | Flexible metal conduit (FMC)   |
| <b>Liquid-tight</b>         | No   |
| <b>Inner Core Material</b>  | Reduced wall steel   |
| <b>Trade Size</b>           | 3/4in  |
| <b>Coil Length</b>          | 100ft/30.4m  |
| <b>UL Rating</b>            | UL-1 Listed  |
| <b>Applicable Standards</b> | <ul style="list-style-type: none"><li>• ANSI/UL-1 Listed</li><li>• Federal specification WW-C-566c</li></ul> |
| <b>Application</b>          | Dry locations  |

---

## Agency Approvals

|                         |   |
|-------------------------|---|
| <b>UL Listed File #</b> | E43113  |
| <b>RoHS Status</b>      | Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below) |
| <b>EU REACH</b>         | <a href="#">View EU REACH document</a>                              |
| <b>Other</b>            | <a href="#">RoHS Statement</a>                                      |