

5661 Cut Sheet



Bryant industrial heavy duty single straight blade receptacle, 15A, 250 VAC, 1-phase, 2-pole, 3-wire, NEMA 6-15, nylon housing, brown.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/5661>

Technical Specifications

Brand	Bryant
Item	Receptacle
Application	Industrial heavy duty
Receptacle Type	Single
Blade Type	Straight
With Cap	No
Self-grounding	Yes
Amperage Rating	15A
Voltage Rating	250 VAC
Number of Phases	1
Number of Poles	2
Number of Wires	3
Wire Size	14-10 AWG solid or stranded
Copper Wire Only	Yes
Configuration	NEMA 6-15
Housing Material	Nylon
Color	Brown

Agency Approvals

UL Listed File #	E2258
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	016215
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document