

# 57005255 Cut Sheet



WERMA audible signal horn with trumpet, 108 dB at 1m, 100 Hz tone frequency, continuous tone(s), 24 VDC, wall mount, ABS/polycarbonate housing, off-white, IP55.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/57005255>

---

## Technical Specifications

<b>Brand</b>	WERMA
<b>Item</b>	Audible signal horn with trumpet
<b>Loudness Decibel</b>	108 dB at 1m
<b>Tone Frequency</b>	100 Hz
<b>Tone Type</b>	Continuous
<b>Touch to Acknowledge</b>	No
<b>Voltage Rating</b>	24 VDC
<b>Mounting</b>	Wall
<b>Housing Material</b>	ABS/polycarbonate
<b>Color</b>	Off-white
<b>IP Rating</b>	IP55

---

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	None
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>