

57005267 Cut Sheet



WERMA audible signal horn with trumpet, 108 dB at 1m, 100 Hz tone frequency, continuous tone(s), 115 VAC, wall mount, ABS/polycarbonate housing, off-white, IP55.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/57005267>

Technical Specifications

Brand	WERMA
Item	Audible signal horn with trumpet
Loudness Decibel	108 dB at 1m
Tone Frequency	100 Hz
Tone Type	Continuous
Touch to Acknowledge	No
Number of Alarms	1
Voltage Rating	115 VAC
Mounting	Wall
Housing Material	ABS/polycarbonate
Color	Off-white
IP Rating	IP55

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/57005267.pdf>
See store item page for other formats.