

57010015 Cut Sheet



Socomec modular fuse holder, accepts Class Midget fuses, 30A, 750 VAC, 1-pole, 18-8 AWG copper only, pressure plate, 35mm DIN rail mount. Package of 12.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/57010015>

Technical Specifications

Brand	Socomec
Item	Fuse holder
Modular	Yes
Blown Fuse Indicator	No
Multi-Wire	No
Accepts Fuse Class	Class Midget
Amperage Rating	30A
Voltage Rating	750 VAC

Number of Poles	1
Conductor Size	18-8 AWG copper only
Conductor Connection Type	Pressure plate
SCCR Rating	200kA SCCR
Fuse Connection Type	Clip with reinforced spring
Mounting	35mm DIN rail
Quantity per Pack	12

Agency Approvals

UL Listed File #	None
UL Recognized File #	E307648
CE	View CE declarations
CSA File #	265615
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/57010015.pdf>
See store item page for other formats.