

57010018-1PK Cut Sheet



Socomec modular fuse holder, accepts Class Midget fuses, 30A, 750 VAC, 3-pole, 18-8 AWG copper only, pressure plate, 35mm DIN rail mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/57010018-1PK>

Technical Specifications

Brand	Socomec
Item	Fuse holder
Modular	Yes
Blown Fuse Indicator	No
Multi-Wire	No
Accepts Fuse Class	Class Midget
Amperage Rating	30A
Voltage Rating	750 VAC
Number of Poles	3
Conductor Size	18-8 AWG copper only
Conductor Connection Type	Pressure plate
SCCR Rating	200kA SCCR
Fuse Connection Type	Clip with reinforced spring
Mounting	35mm DIN rail

Agency Approvals

UL Listed File #	None
UL Recognized File #	E307648
CE	View CE declarations
CSA File #	265615
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document