

# 57050002-1PK Cut Sheet



Socomec modular fuse holder, accepts Class CC fuses, 30A, 600 VAC, 2-pole, 18-8 AWG copper only, pressure plate, 35mm DIN rail mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/57050002-1PK>

## Technical Specifications

<b>Brand</b>	Socomec
<b>Item</b>	Fuse holder
<b>Modular</b>	Yes
<b>Blown Fuse Indicator</b>	No
<b>Multi-Wire</b>	No
<b>Accepts Fuse Class</b>	Class CC
<b>Amperage Rating</b>	30A
<b>Voltage Rating</b>	600 VAC
<b>Number of Poles</b>	2
<b>Conductor Size</b>	18-8 AWG copper only
<b>Conductor Connection Type</b>	Pressure plate
<b>SCCR Rating</b>	200kA SCCR
<b>Fuse Connection Type</b>	Clip with reinforced spring
<b>Mounting</b>	35mm DIN rail

## Agency Approvals

<b>UL Listed File #</b>	E307648
<b>UL Recognized File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	265615
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/2d/57050002-1PK.pdf>  
See store item page for other formats.