

57300067 Cut Sheet



WERMA audible signal horn, 105 dB at 1m, 100 Hz tone frequency, continuous tone(s), 115 VAC, wall mount, ABS plastic housing, light gray, IP65.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/57300067>

Technical Specifications

Brand	WERMA
Item	Audible signal horn
Loudness Decibel	105 dB at 1m
Tone Frequency	100 Hz
Tone Type	Continuous
Touch to Acknowledge	No
Voltage Rating	115 VAC
Mounting	Wall
Housing Material	ABS plastic
Color	Light gray
IP Rating	IP65

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/57300067.pdf>
See store item page for other formats.