

58010 Cut Sheet



Viking jobber-length drill bit and machine tap set, 18 pieces, high-speed steel (HSS), round and square shank, UNF thread type, imperial, number and letter, gold oxide finish, metal index case.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/58010>

Technical Specifications

Brand	Viking	Point Cut	Split
Item	Drill bit and machine tap set	Shank Type	Round and square
Number of Pieces	18	Application	Thread making and hole cutting
Material	High-speed steel (HSS)	For Use On	Stainless steel, iron and steel
Drill Bit Type	Jobber-length	Measurement Type	Imperial, number and letter
Thread Type	UNF	Package Type	Metal index case
Thread	#6-40 UNF, #8-36 UNF, #10-24 UNC, #10-32 UNF, 1/4-28 UNF, 5/16-24 UNF, 3/8-24 UNF, 7/16-20 UNF and 1/2-20 UNF	Set Includes	Includes (9) jobber-length drill bits (wire number size 33, wire number size 29, wire number size 25, wire number size 21, wire number size 3, wire number size 1, letter size Q, 25/64in, 29/64in), (9) machine taps (#6-40 UNF, #8-36 UNF, #10-24 UNC, #10-32 UNF, 1/4-28 UNF, 5/16-24 UNF, 3/8-24 UNF, 7/16-20 UNF, 1/2-20 UNF), durable metal case
Drill Bit Size	Wire number size 33, wire number size 29, wire number size 25, wire number size 21, wire number size 3, wire number size 1, letter size Q, 25/64in and 29/64in		
Finish	Gold oxide		
Point Angle	135 degrees		

Agency Approvals

UL Listed File #	N/A
UL Recognized File #	N/A
UL Hazardous File #	N/A
CE	None
CSA File #	N/A
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement