

# 59381 Cut Sheet



Viking pipe tap, 3/8-18 NPT, high-speed steel (HSS), bright finish.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/59381>

## Technical Specifications

Brand	Viking
Item	Pipe tap
Thread	3/8-18 NPT
Number of Flutes	4
Flute Style	Straight flute
Overall Length	2.6in (66mm)
Tap Drill Size	37/64in
Material	High-speed steel (HSS)
Finish	Bright
For Use On	Stainless steel, iron and steel
Application	Thread making

## Agency Approvals

UL Listed File #	N/A
UL Recognized File #	N/A
UL Hazardous File #	N/A
CE	None
CSA File #	N/A
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	<a href="#">View EU REACH document</a>
Other	<a href="#">RoHS Statement</a>