

5U11B241 Cut Sheet



Metal Work Syntesi Size 1 pneumatic filter-regulator, 1/8in female NPT inlet(s), 1/8in female NPT outlet(s), 0 to 120 psig range, manual/semi-automatic drain, clear technopolymer bowl, bowl guard.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/5U11B241>

Technical Specifications

Brand	Metal Work
Series	Syntesi Size 1
Item	Filter-regulator
Working Fluid	Air
Inlet Port	1/8in female NPT
Outlet Port	1/8in female NPT
Drain Port	G1/8 female BSPP
Pressure Range	0 to 120 psig
Drain Type	Manual/semi-automatic
Bowl Material	Clear technopolymer
Bowl Guard	Yes
Sight Gauge	No
Includes	(2) G1/8 female BSPP ports for gauge or additional outlet and 20 micron filter element

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/5U11B241.pdf>
See store item page for other formats.