

5U11R141 Cut Sheet



Metal Work Syntesi Size 1 pneumatic regulator, 1/8in female NPT inlet(s), 1/8in female NPT outlet(s), 0 to 120 psig range.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/5U11R141>

Technical Specifications

Brand	Metal Work
Item	Regulator
Series	Syntesi Size 1
Working Fluid	Air
Inlet Port	1/8in female NPT
Outlet Port	1/8in female NPT
Pressure Range	0 to 120 psig
Additional Information	(2) G1/8 female BSPP ports for gauge or additional outlet

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/5U11R141.pdf>
See store item page for other formats.