

5U11V10B24L101 Cut Sheet



Metal Work Syntesi Size 1 pneumatic combination unit, valve-filter-regulator-lubricator, 1/8in female NPT inlet(s), 1/8in female NPT outlet(s), 0 to 120 psig range, clear technopolymer bowl, manual/semi-automatic drain, manual shutoff valve.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/5U11V10B24L101>

Technical Specifications

| | |
|-----------------------|-----------------------------------|
| Brand | Metal Work |
| Series | Syntesi Size 1 |
| Item | Combination unit |
| Working Fluid | Air |
| Configuration | Valve-filter-regulator-lubricator |
| Inlet Port | 1/8in female NPT |
| Outlet Port | 1/8in female NPT |
| Pressure Range | 0 to 120 psig |
| Bowl Material | Clear technopolymer |

| | |
|-----------------------------|--|
| Drain Type | Manual/semi-automatic |
| Clog Indicator | No |
| Manual Shutoff Valve | Yes |
| Padlockable | Yes |
| Soft Start Valve | No |
| Pressure Switch | No |
| Includes | (2) G1/8 female BSPP ports for gauge or additional outlet and 20 micron filter element |

Agency Approvals

| | |
|-----------------------------|--|
| UL Listed File # | None |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | View CE declarations |
| CSA File # | None |
| RoHS Status | Yes (See CE Doc) |
| EU REACH | View EU REACH document |

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/5U11V10B24L101.pdf>
See store item page for other formats.