

# 5U13B24L103 Cut Sheet



Metal Work Syntesi Size 1 pneumatic combination unit, filter-regulator-lubricator, 3/8in female NPT inlet(s), 3/8in female NPT outlet(s), 0 to 120 psig range, clear technopolymer bowl, manual/semi-automatic drain.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/5U13B24L103>

## Technical Specifications

<b>Brand</b>	Metal Work
<b>Series</b>	Syntesi Size 1
<b>Item</b>	Combination unit
<b>Working Fluid</b>	Air
<b>Configuration</b>	Filter-regulator-lubricator
<b>Inlet Port</b>	3/8in female NPT
<b>Outlet Port</b>	3/8in female NPT
<b>Pressure Range</b>	0 to 120 psig
<b>Bowl Material</b>	Clear technopolymer

<b>Drain Type</b>	Manual/semi-automatic
<b>Clog Indicator</b>	No
<b>Manual Shutoff Valve</b>	No
<b>Padlockable</b>	No
<b>Soft Start Valve</b>	No
<b>Pressure Switch</b>	No
<b>Includes</b>	(2) G1/8 female BSPP ports for gauge or additional outlet and 20 micron filter element

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	None
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/2d/5u13b24l103.pdf>  
See store item page for other formats.