

5U23B24L103 Cut Sheet



Metal Work Syntesi Size 2 pneumatic combination unit, filter-regulator-lubricator, 3/8in female NPT inlet(s), 3/8in female NPT outlet(s), 0 to 120 psig range, clear technopolymer bowl, manual/semi-automatic drain.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/5U23B24L103>

Technical Specifications

Brand	Metal Work
Series	Syntesi Size 2
Item	Combination unit
Working Fluid	Air
Configuration	Filter-regulator-lubricator
Inlet Port	3/8in female NPT
Outlet Port	3/8in female NPT
Pressure Range	0 to 120 psig
Bowl Material	Clear technopolymer

Drain Type	Manual/semi-automatic
Clog Indicator	No
Manual Shutoff Valve	No
Padlockable	No
Soft Start Valve	No
Pressure Switch	No
Includes	(2) G1/4 female BSPP ports for gauge or additional outlet and 20 micron filter element

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/5U23B24L103.pdf>
See store item page for other formats.