

5U24F20L104 Cut Sheet



Metal Work Syntesi Size 2 pneumatic combination unit, filter-lubricator, 1/2in female NPT inlet(s), 1/2in female NPT outlet(s), clear technopolymer bowl, manual/semi-automatic drain.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/5U24F20L104>

Technical Specifications

Brand	Metal Work
Series	Syntesi Size 2
Item	Combination unit
Working Fluid	Air
Configuration	Filter-lubricator
Inlet Port	1/2in female NPT
Outlet Port	1/2in female NPT
Bowl Material	Clear technopolymer

Drain Type	Manual/semi-automatic
Clog Indicator	No
Manual Shutoff Valve	No
Padlockable	No
Soft Start Valve	No
Pressure Switch	No
Includes	Replaceable 20 micron filter element

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/5u24f20l104.pdf>
See store item page for other formats.