

# 5U24R144 Cut Sheet



Metal Work Syntesi Size 2 pneumatic regulator, 1/2in female NPT inlet(s), 1/2in female NPT outlet(s), 0 to 120 psig range.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/5U24R144>

## Technical Specifications

<b>Brand</b>	Metal Work
<b>Item</b>	Regulator
<b>Series</b>	Syntesi Size 2
<b>Working Fluid</b>	Air
<b>Inlet Port</b>	1/2in female NPT
<b>Outlet Port</b>	1/2in female NPT
<b>Pressure Range</b>	0 to 120 psig
<b>Additional Information</b>	(2) G1/4 female BSPP ports for gauge or additional outlet

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	None
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/2d/5U24R144.pdf>  
See store item page for other formats.