


60002D Cut Sheet



Bryant manual motor controller, open, 60A, 600 VAC, 2-pole, 20hp, UL 508 rated.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/60002D>

Technical Specifications

Brand	Bryant
Item	Manual motor controller
Body Type	Open
Amperage Rating	60A
Voltage Rating	600 VAC
Number of Poles	2
Horsepower Rating	20hp
Wiring Type	Can be wired from the back only
UL Rating	UL 508 rated
Additional Information	Suitable as motor disconnect

Agency Approvals

UL Listed File #	E70402
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	46186
RoHS Status	No
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/60002D.pdf>
See store item page for other formats.