

6003-22-00 Cut Sheet



Atkore Liquid-Tuff 6000 liquid-tight flexible non-metallic conduit, embedded spiral rigid PVC, PVC wall, 3/4in trade size, gray, UL-1660 Listed, 25ft/7.6m coil length.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/6003-22-00>

Technical Specifications

Brand	Atkore
Series	Liquid-Tuff 6000
Item	Conduit
Conduit Type	Liquid-tight flexible non-metallic conduit (LFNC)
Flexibility	Flexible
Liquid-tight	Yes
Inner Core Material	Embedded spiral rigid PVC
Outer Material	PVC wall
Trade Size	3/4in

Outside Diameter	1.050in
Minimum Bend Radius	4.25in
Color	Gray
Coil Length	25ft/7.6m
UL Rating	UL-1660 Listed
Operating Temperature	0 deg F to 176 deg F (-18 deg C to 80 deg C)
UV Resistant	Yes
Applicable Standards	ANSI/UL-1660 Type B
Application	Wet locations

Agency Approvals

UL Listed File #	E26540
CE	None
CSA File #	157782
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement