

6004-30-00 Cut Sheet



Atkore Liquid-Tuff 6000 liquid-tight flexible non-metallic conduit, embedded spiral rigid PVC, PVC wall, 1in trade size, gray, UL-1660 Listed, 100ft/30.4m coil length.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/6004-30-00>

Technical Specifications

Brand	Atkore	Outside Diameter	1.315in
Series	Liquid-Tuff 6000	Minimum Bend Radius	6.5in
Item	Conduit	Color	Gray
Conduit Type	Liquid-tight flexible non-metallic conduit (LFNC)	Coil Length	100ft/30.4m
Flexibility	Flexible	UL Rating	UL-1660 Listed
Liquid-tight	Yes	Operating Temperature	0 deg F to 176 deg F (-18 deg C to 80 deg C)
Inner Core Material	Embedded spiral rigid PVC	UV Resistant	Yes
Outer Material	PVC wall	Applicable Standards	ANSI/UL-1660 Type B
Trade Size	1in	Application	Wet locations

Agency Approvals

UL Listed File #	E26540
CE	None
CSA File #	157782
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement