

# 60MXL025NG Cut Sheet



SureMotion timing belt, 0.08in MXL pitch, 1/4in wide, 60 tooth, 4.8in pitch length (circumference), neoprene, fiberglass reinforced. Package of 3.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/60MXL025NG>

## Technical Specifications

|                     |             |
|---------------------|-------------|
| Brand               | SureMotion  |
| Item                | Timing belt |
| Pitch               | 0.08in MXL  |
| Width               | 1/4in       |
| Number of Teeth     | 60          |
| Pitch length        | 4.8in       |
| Material            | Neoprene    |
| Reinforcement       | Fiberglass  |
| Belt Tensile Rating | 103lb       |
| Quantity per Pack   | 3           |

## Agency Approvals

|                      |  |
|----------------------|--|
| UL Listed File #     | None                                   |
| UL Recognized File # | None                                   |
| UL Hazardous File #  | None                                   |
| CE                   | None                                   |
| CSA File #           | None                                   |
| RoHS Status          | No                                     |
| EU REACH             | <a href="#">View EU REACH document</a> |

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/60MXL025NG.pdf>  
See store item page for other formats.