

61041 Cut Sheet

Viking hand tap, #6-32 UNC, high-speed steel (HSS), bright finish.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/61041>

Technical Specifications

Brand	Viking	Overall Length	2.0in (51mm)
Item	Hand tap	Tap Drill Size	Wire number size 36
Thread	#6-32 UNC	Material	High-speed steel (HSS)
Number of Flutes	3	Finish	Bright
Flute Style	Straight flute	For Use On	Stainless steel, iron and steel
Tap Limit	H3	Application	Thread making

Agency Approvals

UL Listed File #	N/A
UL Recognized File #	N/A
UL Hazardous File #	N/A
CE	None
CSA File #	N/A
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement