

6105323 Cut Sheet



Seifert SoliTherm thermoelectric cooler, 340 BTU/H, 230 VAC operating voltage, 304 stainless steel housing, filter-free, recessed mount. For use with NEMA 4/4X/12 enclosures.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/6105323>

Technical Specifications

Brand	Seifert
Series	SoliTherm
Item	Thermoelectric cooler
Nominal Cooling Capacity	340 BTU/H
Operating Voltage	230 VAC
Frequency	50/60 Hz
Running Current	1.1A
Height	11.02in
Width	13.78in
Depth	7.2in
Mounting	Recessed
Filter-Free	Yes
Housing Material	304 stainless steel
IP Rating	IP66
For Use With	NEMA 4/4X/12 enclosures
Includes	Mounting hardware

Agency Approvals

UL Listed File #	None
UL Recognized File #	SA32278
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document