

# 61071 Cut Sheet

Viking hand tap, #8-36 UNF, high-speed steel (HSS), bright finish.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/61071>

## Technical Specifications

Brand	Viking
Item	Hand tap
Thread	#8-36 UNF
Number of Flutes	4
Flute Style	Straight flute
Tap Limit	H2

Overall Length	2.2in (56mm)
Tap Drill Size	Wire number size 29
Material	High-speed steel (HSS)
Finish	Bright
For Use On	Stainless steel, iron and steel
Application	Thread making

## Agency Approvals

UL Listed File #	N/A
UL Recognized File #	N/A
UL Hazardous File #	N/A
CE	None
CSA File #	N/A
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	<a href="#">View EU REACH document</a>
Other	<a href="#">RoHS Statement</a>