

# 61091 Cut Sheet

Viking hand tap, #10-32 UNF, high-speed steel (HSS), bright finish.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/61091>

## Technical Specifications

|                         |                |                       |                                 |
|-------------------------|----------------|-----------------------|---------------------------------|
| <b>Brand</b>            | Viking         | <b>Overall Length</b> | 2.4in (61mm)                    |
| <b>Item</b>             | Hand tap       | <b>Tap Drill Size</b> | Wire number size 21             |
| <b>Thread</b>           | #10-32 UNF     | <b>Material</b>       | High-speed steel (HSS)          |
| <b>Number of Flutes</b> | 4              | <b>Finish</b>         | Bright                          |
| <b>Flute Style</b>      | Straight flute | <b>For Use On</b>     | Stainless steel, iron and steel |
| <b>Tap Limit</b>        | H3             | <b>Application</b>    | Thread making                   |

## Agency Approvals

|                             |                                                                     |
|-----------------------------|---------------------------------------------------------------------|
| <b>UL Listed File #</b>     | N/A                                                                 |
| <b>UL Recognized File #</b> | N/A                                                                 |
| <b>UL Hazardous File #</b>  | N/A                                                                 |
| <b>CE</b>                   | None                                                                |
| <b>CSA File #</b>           | N/A                                                                 |
| <b>RoHS Status</b>          | Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below) |
| <b>EU REACH</b>             | <a href="#">View EU REACH document</a>                              |
| <b>Other</b>                | <a href="#">RoHS Statement</a>                                      |