

6200-660-AAA7B-A Cut Sheet



Spartan solenoid valve, 2-way, 2-position, N.C., glass-filled nylon body, 1/8in female NPT inlet(s), 1/8in female NPT outlet(s), Cv=0.52, vacuum minimum operating pressure, 120 VAC operating voltage, 18in 22 AWG pigtail.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/6200-660-AAA7B-A>

Technical Specifications

Brand	Spartan
Item	Valve
Working Fluid	Potable water
Valve Type	Solenoid process
Series	6200
IP Rating	IP65
Port Quantity	2-way
Number Of Positions	2
Valve Configuration	N.C.

Action	Single solenoid spring return
Body Material	Glass-filled nylon
Inlet Port	1/8in female NPT
Outlet Port	1/8in female NPT
Flow Coefficient	0.52
Maximum Operating Pressure	75 psi
Minimum Operating Pressure	Vacuum
Operating Voltage	120 VAC
Electrical Connection	18in 22 AWG pigtail

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/6200-660-AAA7B-A.pdf>
See store item page for other formats.