

6207-24-00 Cut Sheet



Atkore Liquid-Tuff 6200 liquid-tight flexible metallic conduit, galvanized low carbon steel, PVC jacket, 2in trade size, gray, UL-360 Listed, 50ft/15.2m coil length.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/6207-24-00>

Technical Specifications

Brand	Atkore	Outside Diameter	2.375in
Series	Liquid-Tuff 6200	Minimum Bend Radius	11.1in
Item	Conduit	Color	Gray
Conduit Type	Liquid-tight flexible metallic conduit (LFMC)	Coil Length	50ft/15.2m
Flexibility	Flexible	UL Rating	UL-360 Listed
Liquid-tight	Yes	Operating Temperature	-40 deg F to 176 deg F (-40 deg C to 80 deg C)
Inner Core Material	Galvanized low carbon steel	UV Resistant	Yes
Outer Material	PVC jacket	Applicable Standards	ANSI/UL-360 and CSA C22.2 No 56
Trade Size	2in	Application	Wet locations

Agency Approvals

UL Listed File #	E26540
CE	None
CSA File #	157782
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement