

# 6222-6J001-AAC3C-A Cut Sheet



Spartan solenoid valve, 2-way, 2-position, N.C., low lead brass body, 3/8in female NPT inlet(s), 3/8in female NPT outlet(s), Cv=0.31, 150 psi maximum operating pressure, 24 VDC operating voltage, 18mm DIN style wiring plug.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/6222-6J001-AAC3C-A>

## Technical Specifications

|                     |                               |
|---------------------|-------------------------------|
| Brand               | Spartan                       |
| Series              | 6222                          |
| Item                | Valve                         |
| Working Fluid       | Potable water                 |
| Valve Type          | Solenoid process              |
| Port Quantity       | 2-way                         |
| Number Of Positions | 2                             |
| Valve Configuration | N.C.                          |
| Operator Type       | Direct acting                 |
| Action              | Single solenoid spring return |
| Body Material       | Low lead brass                |

|                            |                            |
|----------------------------|----------------------------|
| IP Rating                  | IP65                       |
| Inlet Port                 | 3/8in female NPT           |
| Outlet Port                | 3/8in female NPT           |
| Flow Coefficient           | 0.31                       |
| Maximum Operating Pressure | 150 psi                    |
| Minimum Operating Pressure | Vacuum                     |
| Operating Voltage          | 24 VDC                     |
| Electrical Connection      | 18mm DIN style wiring plug |

## Agency Approvals

|                      |                        |
|----------------------|------------------------|
| UL Listed File #     | None                   |
| UL Recognized File # | None                   |
| UL Hazardous File #  | None                   |
| CSA File #           | None                   |
| RoHS Status          | Yes (See CE Doc)       |
| EU REACH             | View EU REACH document |

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/2d/6222-6J001-AAC3C-A.pdf>  
See store item page for other formats.