

6222-6K001-AAB3B-A Cut Sheet



Spartan solenoid valve, 2-way, 2-position, N.C., low lead brass body, 1/4in female NPT inlet(s), 1/4in female NPT outlet(s), Cv=0.52, 90 psi maximum operating pressure, 24 VDC operating voltage, 18in 22 AWG pigtail.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/6222-6K001-AAB3B-A>

Technical Specifications

Brand	Spartan
Series	6222
Item	Valve
Working Fluid	Potable water
Valve Type	Solenoid process
Port Quantity	2-way
Number Of Positions	2
Valve Configuration	N.C.
Operator Type	Direct acting
Action	Single solenoid spring return
Body Material	Low lead brass

IP Rating	IP65
Inlet Port	1/4in female NPT
Outlet Port	1/4in female NPT
Flow Coefficient	0.52
Maximum Operating Pressure	90 psi
Minimum Operating Pressure	Vacuum
Operating Voltage	24 VDC
Electrical Connection	18in 22 AWG pigtail

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/6222-6K001-AAB3B-A.pdf>
See store item page for other formats.