6320-0000-0000 Cut Sheet

AUTOMATIONDIRECT.com
www.automationdirect.com

Trumeter electrical hour meter, 8mm 8-digit LCD, discrete input, remote reset, rectangular flush mount with clip, screw terminals.

For complete product information, please see this item on our store at the following link:

https://www.automationdirect.com/pn/6320-0000-0000

Technical Specifications

Brand	Trumeter
Item	Hour meter
Counter Type	Electrical
Count Direction	Up
Display Type	LCD
Display Size	8mm 8-digit
Display Units	Hours and tenths
Reset	Remote
Input Signal	Discrete
Mounting	Panel

Mounting Type	Rectangular flush mount with clip
Mounting Hole Size	1/32 DIN
Connector Type	Screw terminals
Additional Information	NEMA 4/4X, 12 & IP66 compliant from the front when using the optional gasket
Dangerous Goods	• Battery Installed: Yes • Packaging Instructions: 970 • UN Number: UN3091 • Hazard Type: Lithium Battery • Battery Type: Other • Generic Battery: CR2032

Agency Approvals

UL Listed File #	None
UL Recognized File #	E36690
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings

2D Drawing PDF Link:
https://cdn.automationdirect.com/static/drawings/6320-0000-0000.pdf
See store item page for other formats.