

6320-1000-0000 Cut Sheet



Trumeter electrical hour meter, 8mm 8-digit LCD, 3-30 VDC input, remote reset, rectangular flush mount with clip, screw terminals.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/6320-1000-0000>

Technical Specifications

Brand	Trumeter
Item	Hour meter
Counter Type	Electrical
Count Direction	Up
Display Type	LCD
Display Size	8mm 8-digit
Display Units	Hours and tenths
Reset	Remote
Input	3-30 VDC
Mounting	Panel
Mounting Type	Rectangular flush mount with clip
Mounting Hole Size	1/32 DIN
Connector Type	Screw terminals
Additional Information	NEMA 4/4X, 12 & IP66 compliant from the front when using the optional gasket
Dangerous Goods	<ul style="list-style-type: none">• Battery Installed: Yes• Packaging Instructions: 970• UN Number: UN3091• Hazard Type: Lithium Battery• Battery Type: Other• Generic Battery: CR2032

Agency Approvals

UL Listed File #	None
UL Recognized File #	E36690
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document