

# 64580075 Cut Sheet



WERMA buzzer element, 85 dB at 1m, 1.8 kHz tone frequency, continuous/pulse tone(s), 24 VAC/VDC, polycarbonate housing, black, IP65. For use with WERMA 70mm stack light elements.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/64580075>

## Technical Specifications

<b>Brand</b>	WERMA
<b>Item</b>	Buzzer element
<b>Loudness Decibel</b>	85 dB at 1m
<b>Tone Frequency</b>	1.8 kHz
<b>Tone Type</b>	Continuous/pulse
<b>Touch to Acknowledge</b>	No
<b>Voltage Rating</b>	24 VAC/VDC
<b>Housing Material</b>	Polycarbonate
<b>Color</b>	Black
<b>IP Rating</b>	IP65
<b>For Use With</b>	WERMA 70mm stack light elements

## Agency Approvals

<b>UL Listed File #</b>	E164155
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	None
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>