

64580075 Cut Sheet



WERMA buzzer element, 85 dB at 1m, 1.8 kHz tone frequency, continuous/pulse tone(s), 24 VAC/VDC, polycarbonate housing, black, IP65. For use with WERMA 70mm stack light elements.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/64580075>

Technical Specifications

| | |
|-----------------------------|---------------------------------|
| Brand | WERMA |
| Item | Buzzer element |
| Loudness Decibel | 85 dB at 1m |
| Tone Frequency | 1.8 kHz |
| Tone Type | Continuous/pulse |
| Touch to Acknowledge | No |
| Voltage Rating | 24 VAC/VDC |
| Housing Material | Polycarbonate |
| Color | Black |
| IP Rating | IP65 |
| For Use With | WERMA 70mm stack light elements |

Agency Approvals

| | |
|-----------------------------|--|
| UL Listed File # | E164155 |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | View CE declarations |
| CSA File # | None |
| RoHS Status | Yes (See CE Doc) |
| EU REACH | View EU REACH document |
| Other | None |