

64580077 Cut Sheet



WERMA buzzer element, 85 dB at 1m, 1.8 kHz tone frequency, continuous/pulse tone(s), 115 VAC, polycarbonate housing, black, IP65. For use with WERMA 70mm stack light elements.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/64580077>

Technical Specifications

Brand	WERMA
Item	Buzzer element
Loudness Decibel	85 dB at 1m
Tone Frequency	1.8 kHz
Tone Type	Continuous/pulse
Touch to Acknowledge	No
Voltage Rating	115 VAC
Housing Material	Polycarbonate
Color	Black
IP Rating	IP65
For Use With	WERMA 70mm stack light elements

Agency Approvals

UL Listed File #	E164155
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document